
# baumann








break | box

THE AUTOMATION FOR CERAMIC SUBSTRATE SINGULATION



# baumann



## break box

As an automation and robotics specialist, baumann offers ceramic substrate singulation and assembly solutions.

The latest baumann development revolutionizes the singulation of hybrids. Based on intensive research together with market leading manufacturers of substrate ceramics now high reject costs, conchoidal fractures and special type related systems belong to history.

The patented baumann breaklbox singulates laser scribed and scored DBC, LTCC, Thick Film Hybrids, HTCC type ceramic panels et al.

The handling and singulation is unique. A robot moves new panels in the singulation position without any fixation or mechanical stopper.

The innovative and fault-tolerant singulation method reduces the breaking forces by software driven kinematics to a minimum.

Another highlight is the easy to use configuration of new panel types. Within minutes a new panel type is stored with its design parameters in the software library and can directly be used for a type exchange without any mechanical retrofitting.

The baumann breaklbox is available as a standalone or inline cell. A variety of options simplifies the integration in assembly lines.

Look and see the quality and the range of functions of the singulation method. You can test the singulation quality also for your own ceramic substrates in our technical laboratory.

### **Technical Data**

| Hybrid panel size                           | 4" x 4" - 9" x 8"         |
|---|---------------------------|
| Substrate thickness                         | 0,25 – 1mm                |
| Single substrate size                       | ≥ 5 mm x 5 mm             |
| Substrate types                             | DBC, LTCC, DSH, HTCC u.a. |
| Cycle time single substrate                 | 3,5 - 5 sec               |
| Component distance to soring/laser scribing | > 0,2 - 0,5 mm            |

92224 Amberg, Germany Tel.: (+49) 9621 6754-0 Fax: (+49) 9621 6754-922 info@baumann-automation.com www.baumann-automation.com Room 103, Building No. 3 No. 115, Xin Junhuan Road, Minhang District 201114 Shanghai, China Tel.: (+86) 21 3331 5500-808 china@baumann-automation.com www.baumann-automation.com

### S.C. Baumann Automation S.R.L.

131C Traian Vuia Street 400397 Cluj-Napoca, Cluj, Romania Tel.: (+40) 735 171 930 office.romania@baumann-automation.com

#### **Vectralis-Baumann Automation**

Industria Naviera 168 45069 Zapopan, Jal., Mexico Tel.: (+52) 33 31-65-20-00 info@vectralis.com www.vectralis.com